

History and release notes for the Power Meter R&S®NRP2

Contents

Contents	1
NRP driver history.....	1
Supported Interfaces	3
Overview	3
Channels and Measurements	3
LabWindows/CVI	3
Additional Help	3
VXIplug&play Instrument Driver for C#, C/C++, Visual Basic .NET, VEE, etc.....	3
Additional Help	3
Additional Information.....	3

NRP driver history		
Revision	Date	Note
2.3.0	11/2010	Modifications: - Added support for NRP2 - 64bit version installtion - Fixed rsnrp_meas_readScope
2.2.1	01/2009	Modifications: - Fixed installer
2.2	08/2004	Modifications: - Fixed function rsnrp_tslot_setTimeSlotCount
2.1	01/2004	Modifications: Added new function for firmware revision 3.01: -rsnrp_display_setUpdate -rsnrp_display_getUpdate -rsnrp_display_setShowErrorlist -rsnrp_display_getShowErrorlist -rsnrp_error_setExtendedMessage -rsnrp_error_getExtendedMessage -rsnrp_system_setBeepOnOverload -rsnrp_system_getBeepOnOverload -rsnrp_system_setKeyclick -rsnrp_system_getKeyclick -rsnrp_meas_configureMathExt -rsnrp_meas_getMathPrimaryEval -rsnrp_meas_getMathSecondaryEval -rsnrp_meas_getMathPrimaryGate -rsnrp_meas_getMathSecondaryGate -rsnrp_trigger_setSynchronize -rsnrp_trigger_getSynchronize Updated function: -rsnrp_meas_configureMath Changed: -Checking of connected sensors

NRP driver history		
Revision	Date	Note
2.0	05/2003	Modifications: Initial Release, except core functions all is new
1.0	02/2003	Beta Release - Only Core functions are supported

Supported Interfaces

The current revision of instrument driver supports interfaces:

- IEEE 488.2 (IEC-625, GPIB)
- VXI-11
- USB (Requires National Instruments VISA 4.x or newer)

Overview

Channels and Measurements

The term channel corresponds to the sensors of the R&S NRP. Channels are used for data acquisition, their output are power values in W. Settings related to this are the correction parameters like frequency, offset and duty cycle and parameters related to averaging, trigger and ranging. They can be set through the Channel interfaces, independantly for every channel. Also there are low level methods to start measurements in channels and retrieve the results.

The measurement result is calculated in a second step from the data of one or two channels, using a mathematical operation like quotient or a function like the formula to calculate a standing wave ratio from incident and reflected power. The result is converted to a selectable unit. Finally the result can be compared to upper and lower limit values for supervision purposes. Settings related to this second step can be set through the Measurement interfaces. Also functions for configuring a complete measurement including channel settings are available there.

The R&S NRP has upto 4 channels, depending on installed options. The number of available channels can be queried with `rsnrp_chans_getCount`

LabWindows/CVI

Additional Help

The LabWindows/CVI instrument driver consists of a ZIP archive containing the driver sources. In addition, the instrument driver documentation is also included in compressed HTML format (Windows CHM help file) and stored together with the driver sources.

VXIplug&play Instrument Driver for C#, C/C++, Visual Basic .NET, VEE, etc.

Additional Help

In addition, the instrument driver documentation is also included in compressed HTML format (Windows CHM help file) and stored together with the driver sources in the `~\VXI\pnp\WinNT\rsnrp` directory.

Additional Information

For more information regarding the VXIPnP instrument drivers, please read the `readme.txt` file that comes with each driver.